

# WheelWatch


Non-contact high speed monitoring of wheel motion on a moving vehicle or in a test station



MEASURE THE ADVANTAGE



...AICON  
3d.systems



# WheelWatch

Non-contact high speed monitoring of wheel motion on a moving vehicle or in a test station

## Vehicle development for optimal driving characteristics

Chassis design is very important to new car development as it ensures optimal driving characteristics. Choosing the right design parameters requires extensive testing. For example, wheel housing design must allow sufficient clearance for various types of tires and their particular movements, and each wheel must be monitored to see how it behaves under extreme driving conditions or on bad pavements. Past studies have relied on mechanical monitoring devices which are complex in handling and may influence the driving behavior.



WheelWatch is based on a camera system that does not require a mechanical connection between sensor and wheel

M E A S U R E T H E


WheelWatch provides a revolutionary approach to wheel monitoring. Due to its functional principle, it offers many advantages, facilitates wheel monitoring and delivers more exact measurement results.

## High speed camera MoveInspect HF

WheelWatch is built around MoveInspect HF which consists of a high-resolution high speed digital camera, an integrated high performance flash and an image analysis processor. The integrated high speed digital camera features extremely short shutter speeds of just a few micro-seconds that are necessary for long duration tests. The high quality camera also ensures the system is robust and stable over time.

It provides data at a frequency of 490 Hz, ideal for studying and optimizing static and dynamic chassis parameters. Measurements are controlled automatically and may be collected over long periods of time. The triggering function ensures that multiple sensors are fully synchronized.

The camera can be mounted at a distance of less than 500 mm (20 in) from the fender. The camera processor uses TCP/IP protocol to communicate with the laptop computer which controls the system. The computer is placed in the test vehicle. The vehicle 12 Volt power system provides power during the test drive.



## A D V A N T A G E

### Functional principle

For the measurement of wheel movements, one camera for each wheel is mounted so that the wheel as well as part of the surrounding fender is visible. Special optical targets applied to the fender define the vehicle coordinate system. A lightweight carbon fiber wheel adapter is fixed to the wheel.




Carbon fiber wheel adapter

The position of the camera does not have to be stable as WheelWatch recalculates its position continuously using the reference targets on the vehicle fender. The wheel movement measurements are always provided in the vehicle coordinate system. Movements of the camera or camera mount do not influence measurement results, making the system inherently more stable than competing systems.

The driver manually triggers the beginning and end of a measurement session. No other interaction with WheelWatch is required. The high speed camera collects wheel measurements at a rate of up to 490 times per second.

The image processor analyzes the digital images in real time and passes the measurement values to the notebook computer. Wheel target positions and target trajectories are available shortly after the image acquisition. In addition, WheelWatch computes all six degrees of freedom of the wheel in the vehicle coordinate system.



WheelWatch measurement results

## WheelWatch advantages

WheelWatch with MoveInspect HF has been developed in close cooperation with the automotive industry, and the system has been designed to provide the features and functionality that are most beneficial for this application.

### Short setup time

A major requirement is fast and easy system setup. The MoveInspect HF camera is designed to be mounted quickly on the vehicle without the requirement of sophisticated tools such as tail lifts. Assembly of a four camera system, mounting frame, wheel adapters, and calibration and referencing to the vehicle coordinate system takes less than one hour. The system is ready to begin making measurements immediately after installation.

### Measurement accuracy

WheelWatch measures wheel movements for a vehicle traveling at speeds of up to 250 km per hour (160 mph). The system is also capable of observing extreme driving maneuvers. Points are measured to an accuracy of about  $\pm 0.1$  mm (0.004 in) and angles to an accuracy of about  $\pm 0.015^\circ$ .

### Simultaneous measurement of several wheels

Several cameras may be precisely synchronized. WheelWatch may also be synchronized with other measurement devices. In this case, the cameras can either be controlled by an external synchronization signal or they can deliver the master signal themselves for all sensors applied in the test. In addition, each individual measurement value is time stamped. Thus, the synchronized application on several wheels and with other measurement sensors is possible.

### Integration into test stations

The WheelWatch system is particularly suited for integration into vehicle test stations. Data acquisition between numerous cameras over multiple axles and even with other sensor types may be precisely synchronized. WheelWatch saves the measurement data digitally, making these suitable for database storage. Data may be converted from digital to analog during tests if real time machine control is required. An optional data router allows the computer to control WheelWatch system functions via TCP/IP.



Work flow: Setup of WheelWatch in a few steps

### No mechanical connection between the sensor and wheel

Measurements are non-contact and require no mechanical connection to the wheel. Consequently, driving characteristics of the vehicle are not influenced by the measurement equipment, and steering motion is not restricted in any way. WheelWatch completely overcomes the disadvantage of other wheel monitoring methods because there is no risk of creating erroneous measurements due to the mechanical connection between sensor and wheel.

### Low weight

No heavy analysis units, batteries or controllers that may influence driving behavior are required, and the camera mount does not need high stability. Light weight mounting components can be used, which eliminates any significant influence on driving behavior.

### One reference for all wheels

With WheelWatch, the four wheels can be captured in a joint coordinate system. Thus it is also possible to detect motion wheel-to-wheel.

### Extendable for new measuring tasks

WheelWatch belongs to AICON's MoveInspect Technology, which brings together a wide range of optical measuring technologies into one high-performance modular system. That brings along a vast advantage: By extending the system with additional components and software modules from the MoveInspect Technology, you can simply adapt it to execute new tasks (e. g. door slam testing or recording of engine movements). Follow-up investments for additional complete systems are no longer necessary.

# Specifications

for test drives and test stations



<b>System</b>	<b>WheelWatch</b>
System components	per axle 2 MoveInspect HF cameras and 2 CFK wheel adapters, mounting frame, accessory set including targets, sync-box, and controlling computer with WheelWatch software
<b>Camera</b>	<b>MoveInspect HF</b>
Type of camera	high speed CMOS camera
Resolution	1280 x 1024 pixels
Max. vision frequency	490 Hz
Exposure time	10 $\mu$ s - 1 s
Lens	high performance lens, f = 10 mm, minimal distortion
Flash	high performance LED ringlight, 10 - 100 $\mu$ s
Data transmission	TCP/IP
Synchronization	digital time stamp / external trigger signal < 5 $\mu$ s / master for synchronization
Power supply	test drive: 12 Volt vehicle power system; power consumption: 26 W for 2 cameras; test station: 90 - 240 Volt
Weight	1.5 kg
<b>Wheel adapter</b>	
Material	carbon fiber
Diameter	400 mm (16")
Weight	< 400 g (< 1 lb)
Targets	ANCO on retro reflective film High Gain 7610
<b>Software</b>	<b>Module WheelWatch</b>
	<ul style="list-style-type: none"> <li>- camera calibration</li> <li>- axle calibration</li> <li>- determination of reference points</li> <li>- transformation in vehicle coordinate system</li> <li>- data transfer via data file, analog or digital (TCP/IP)</li> <li>- calculation of axle and wheel parameters</li> </ul>
<b>Controlling computer</b>	
Test drive	notebook (Microsoft® Windows® 7)
Test station	desktop (Microsoft® Windows® 7)
<b>System parameters</b>	
Position accuracy: X, Y, Z	$\pm$ 0.1 mm (0.004")
Angular accuracy	$\pm$ 0.015°
Measurement volume	1 m x 1 m x 0.5 m (40" x 40" x 20")
Distance camera/wheel adapter	approx. 0.5 m (20")
Measurement range (track/camber)	$\pm$ 45°
Spin angle range	unlimited
Acquisition frequency	490 Hz



# WheelWatch

Non-contact high speed monitoring of wheel motion on a moving vehicle or in a test station

## WheelWatch – a system of AICON's MoveInspect Technology

MoveInspect Technology brings together a wide range of optical measuring technologies into one high-performance modular system. That means that you can combine the individual components such as sensor, probe and computer with the appropriate software.

Thus MoveInspect Technology is a powerful and versatile CMM for probing, tracking and targeting. And as all components are portable, you can always measure right on-site.

A unique investment – in every respect.

MEASURE THE ADVANTAGE



Headquarters  
AICON 3D Systems GmbH  
Biberweg 30 C  
D-38114 Braunschweig  
tel. +49 (0)531 58 000 58  
fax +49 (0)531 58 000 60  
info@aicon.de

AICON Benelux  
Basbellain, Luxembourg  
tel. +352 20 88 01 17  
benelux@aicon.de

AICON France  
tel. +33 (0) 3 63 53 49 00  
france@aicon.de

AICON Asia LLC  
Seongnam, Gyeonggi-do  
(Seoul Area), Korea  
tel. +82 31 607 4040  
asiapacific@aicon.de

China Showroom  
Shanghai, China  
tel. +86 21 51079116 ext. 211  
china@aicon.de

AICON North America  
Plymouth/Michigan, USA  
tel. +1 734 787 4799  
northamerica@aicon3d.com

[www.aicon3d.com](http://www.aicon3d.com)  
[www.moveinspect-technology.com](http://www.moveinspect-technology.com)